



**SAFETY SYSTEM®**  
YOUR PROTECTOR

Sir Safety System S.p.A. Single-member company  
Wholly-owned subsidiary of Sir Holding Srl  
Via dei Fornaciai, 9 - Santa Maria degli Angeli  
06081 Assisi - Perugia - Italy  
Tel.+39 075.8043737 - Fax +39 075.8048686

VAT Nr. IT 03359340548  
Viale Europa 74  
20090 Cusago Milano  
Tel. +39 02.90394575  
Fax +39 02.90394441

TECHNICAL SHEET

export@sirsafety.com  
www.sirsafety.com



UNI EN ISO 9001:2015  
UNI EN ISO 14001:2015  
UNI EN ISO 45001:2018

<b>Name: TONGA low shoe</b>	<b>Code: MB3013ZC</b>	<b>MB30 FOOTWEAR - SIR FUTURE SERIES POWERED BY RESPONDER TECHNOLOGY</b>
-----------------------------	-----------------------	--

**Description**

Low shoe with an ultra-dynamic design, featuring aluminium toecap and composite midsole, PS type, with constant thickness. Fitted with Action Nubuck leather upper equipped with "Faster" quick lacing system and reflective inserts. E-TPU Responder/rubber outsole provides an excellent elasticity and cushioning effect: the midsole made of expanded thermoplastic polyurethane spans the entire sole of the foot, offering flexibility and full responsive cushioning. The rubber outsole, thanks to its deep longitudinal grooves, accentuates the flexibility of the sole and ensures excellent grip on all types of surfaces. SRC slip-resistant.

The RESPONDER insole is composed of a compound that binds together thousands of E-TPU beads with high elasticity and resilience properties. Lined and perforated in the plantar area with outstanding anti-shock properties. Antistatic.

The polyester mesh lining features excellent draining capacity thanks to its fabric and structure with high absorbing capacity.



**Main features:**

- The patented RESPONDER technology used in the midsole and insole, provides outstanding responsive cushioning, extreme lightness and flexibility over the entire surface of the foot, thus assuring excellent performance even after prolonged and intense use.
- Prismatic high-intensity iridescent reflective inserts for extra visibility in low-light conditions.
- The heel stabilizer prevents foot fatigue and improves foot stability.
- The additional overcap protects the shoe from shocks.
- The "Faster" quick lacing system allows to adjust the fit perfectly, making the lacing more even and keeping the tension constant over time.

The product has been designed and manufactured to comply with Regulation (EU) 2016/425 and subsequent amendments.

Update 20/01/2025 - ESD performance available from lots chronologically subsequent to batch no. 827472409.

The original footbed supplied with the shoe can be replaced, without voiding the EN ISO 20345, by the orthopedic footbed SENSOPED ESD by Franz Seidel GmbH, which is compliant with the standard DGUV 112-191.  
 Franz Seidel GmbH | 93047 Regensburg, Germany | P. +49 (0) 94151598 | info@schuh-seidl.de | www.schuh-seidl.de

Category <b>II</b>	Colours <b>BLACK/GREY</b>	Available Sizes In stock: 35 - 48
Quantity/Carton	EC Standards	Important Information



**SAFETY SYSTEM®**  
YOUR PROTECTOR

**Sir Safety System S.p.A. Single-member company**  
Wholly-owned subsidiary of Sir Holding Srl  
Via dei Fornaciai, 9 - Santa Maria degli Angeli  
06081 Assisi - Perugia - Italy  
Tel.+39 075.8043737 - Fax +39 075.8048686

VAT Nr. IT 03359340548  
Viale Europa 74  
20090 Cusago Milano  
Tel. +39 02.90394575  
Fax +39 02.90394441

TECHNICAL SHEET

export@sirsafety.com  
www.sirsafety.com



UNI EN ISO 9001:2015  
UNI EN ISO 14001:2015  
UNI EN ISO 45001:2018

10

EN ISO 20345  
Safety Class:S3S FO SR



EN 61340



DGUV 112-191



Dexterity

The footwear should be stored in a cool dry place, far from heat sources and direct light. Make sure footwear is in good condition, before use. If the shoes are damaged, replace them.

Clean the footwear with a soft brush and water.

Storage and cleaning